



**Compound emergency flushing eye washer**

The emergency flushing eye washer is manufactured in accordance with GB/T38144.1-2019 ANSI Z358.1-2009 standard.

Widely used in petroleum, chemical, electric power, electronics, pharmaceutical and port industries and other workplace application.

First, use environment:

1. A place where hazardous substances, such as chemicals, dangerous liquids, solids, and gases, are sprayed.
2. Places where chemical fires are likely to occur.

二、 Technical parameters

|                                      |   |
|--------------------------------------|---|
| Main material: SS304 stainless steel | Inlet: thread in DN25 / thread in DN15                          |
| Surface treatment: mirror polishing  | Drainage outlet: internal thread in DN32                        |
| Main pipeline diameter: ⑦ 32mm       | Flushing flow rate: 76L / min                                   |
| Usage temperature: 5-40℃             | Wash your face / eye washing flow: 1l. 4L/min eye washing water |
| Function: eye flushing + eye washing | Flow rate: 1.5 L/min  |
| Working pressure: 0.2-0.4Mpa         |   |

Use medium: drinking water at room temperature and in line with sanitary grade standards

Spray head: 260mm, material SS304, stamping and stretching process production!

Washing basin: 260mm, material SS304, rotary rolling edge process, concentrated water concentration, to prevent splashing!

III. warm tips:

1. This product is only used to temporarily slow down the harm of harmful substances to the body in an emergency. It is not a medical device. Please follow the doctor's guidance for further treatment.
2. In cold areas in the north (such as outdoor installation), it should be considered to install anti-freezing measures!
3. It is recommended to set maintenance valves and filters at the water inlet!

|      |                           |                                 |           |          |
|------|---------------------------|---------------------------------|-----------|----------|
| 16   | Eyewash valve             | DN15                            | SS304+ABS | 1        |
| 15   | Flush the showerhead      | Φ260x0.8                        | SS304+ABS | 1        |
| 14   | Flush the sprinkler bend  | Φ32x2.5mm                       | SS304+ABS | 1        |
| 13   | Flush ball valve          | DN25                            | SS304+ABS | 1        |
| 12   | Flush into the water pipe | Φ32x2mm                         | SS304+ABS | 1        |
| 11   | Handle                    | Warning yellow                  | ABS       | 1        |
| 10   | Assembly                  | All in one                      | SS304+ABS | 1        |
| 9    | Eyewash washbasin         | Φ260x0.8mm                      | SS304+ABS | 1        |
| 8    | Drainage tee              | DN32                            | SS304+ABS | 1        |
| 7    | Expansion screws          | M8x10mm                         | SS304+ABS | 3        |
| 6    | Install the base          | Φ42x2x590mm                     | SS304+ABS | 1        |
| 5    | Eyewash drain             | Φ200x2mm                        | SS304+ABS | 1        |
| 4    | Push board                | Warning yellow                  | SS304+ABS | 1        |
| 3    | Eyewash nozzle            | The flow rate is not adjustable | ABS       | 1        |
| 2    | Eyewash inlet pipe        | Φ32x2x590mm                     | SS304+ABS | 1        |
| 1    | Safety warning signs      | Warning green                   | SS304+ABS | 1        |
| Name | Name                      | Specifucadtions                 | Material  | Quantity |